



FWB51S

FWB encl.,univers,5-rows 60 modules cl.II IP44 w.plain door, 800x300x161mm,QC

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Protection main switch No

Configuration

Number of modules 60

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Insertion depth 161 mm

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 800 mm

Installation height 800 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 1 mm

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Copper weight of the product 0.042 kg

Colour white

RAL colour RAL 9010 - Pure white

Installation, mounting

Subject to technical modifications

Suitable for outdoor use

No

Connection

Number of conduit inlets

4

Settings

Enclosure type

Field distributor surface mounted

Equipment

Number of rows

5

Quantity of section in width

1

Number of keys

1

Quantity of rails

5

Can be accessorized

Yes

Number of openings for flange plates

2

Extension possible

Yes

Earthing terminal block

Yes

Neutral terminal block

Yes

Signal passing door

No

Standards

GWT Glow wire test

750 °C

European directive WEEE

concerned

Protection class according to IEC-61140

II

Safety

Protection index IP

IP44

Protection class

isol.class II