



FWB52GS

FWB encl. univers,surface mount.,IP44,classII,w. transp.door,800x550x161mm,QC

## Technical properties

### Architecture

Fixing mode surface-mounting

### Functions

With a pipe-in lead Yes

### Configuration

Number of modules 72

### Compatibility

Suitable for Multimedia No

### Electric current

Rated current 125 A

### Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 800 mm

Installation height 800 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

### Cover, door

Number of keylock of the door 1

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door Yes

### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

### Installation, mounting

Suitable for outdoor use No

### Equipment

Number of rows 10

Quantity of section in width	2
Number of keys	1
Quantity of rails	10
Can be accessorized	Yes
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No