



FWB52S

FWB encl.,univers,5-rows 120 modules cl.II IP44 w.plain door, 800x550x161mm,QC

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Protection main switch No

Configuration

Number of modules 120

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Insertion depth 161 mm

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 800 mm

Installation height 800 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Copper weight of the product 0.081 kg

Colour white

RAL colour RAL 9010 - Pure white

Installation, mounting

Suitable for outdoor use No

Subject to technical modifications

Connection

Number of conduit inlets	8
--------------------------	---

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	5
Quantity of section in width	2
Number of keys	1
Quantity of rails	10
Can be accessorized	Yes
Number of openings for flange plates	4
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

Standards

GWT Glow wire test	750 °C
European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

Protection index IP	IP44
Protection class	isol.class II
