



FWB53S

FWB encl.,univers,5-rows 180 modules cl.II IP44 w.plain door, 800x800x161mm,QC

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Protection main switch No

Configuration

Number of modules 180

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 800 mm

Installation height 800 mm

Width of installed product 800 mm

Width in division units 36

Thickness of sidewall material 1 mm

Cover, door

Type of door closing Hinged pattern handle and bar locking

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Copper weight of the product 0.123 kg

Colour white

RAL colour RAL 9010 - Pure white

Installation, mounting

Suitable for outdoor use No

Subject to technical modifications

Connection

Number of conduit inlets	12
--------------------------	----

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	5
Quantity of section in width	3
Number of keys	1
Quantity of rails	15
Can be accessorized	Yes
Number of openings for flange plates	6
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

Standards

GWT Glow wire test	750 °C
European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

Protection index IP	IP44
Protection class	isol.class II
