



FWB54S

**FWB encl.,univers,5-rows 240 modules cl.II IP44 w.plain door, 800x1050x161mm,QC**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

Protection main switch No

**Configuration**

Number of modules 240

**Compatibility**

Suitable for Multimedia No

**Electric current**

Rated current 125 A

**Dimensions**

Insertion depth 161 mm

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 800 mm

Installation height 800 mm

Width of installed product 1050 mm

Width in division units 48

Thickness of sidewall material 1 mm

**Cover, door**

Type of door closing Hinged pattern handle and bar locking

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Copper weight of the product 0.162 kg

Colour white

RAL colour RAL 9010 - Pure white

**Installation, mounting**

Subject to technical modifications

---

Suitable for outdoor use

No

---

**Connection**

---

Number of conduit inlets

16

---

**Settings**

---

Enclosure type

Field distributor surface mounted

---

**Equipment**

---

Number of rows

5

---

Quantity of section in width

4

---

Number of keys

1

---

Quantity of rails

20

---

Can be accessorized

Yes

---

Number of openings for flange plates

8

---

Extension possible

Yes

---

Earthing terminal block

Yes

---

Neutral terminal block

Yes

---

Signal passing door

No

---

**Standards**

---

GWT Glow wire test

750 °C

---

European directive WEEE

concerned

---

Protection class according to IEC-61140

II

---

**Safety**

---

Protection index IP

IP44

---

Protection class

isol.class II