



FWB61

FWB encl.,univers,6rows 72 mod cl.II IP44,plain door,950x300x161mm,brass term.

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 72

Compatibility

Suitable for Multimedia No

Electric current

Rated current 125 A

Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 950 mm

Installation height 950 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 1 mm

Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Installation, mounting

Suitable for outdoor use No

Subject to technical modifications

Connection

Number of conduit inlets	4
--------------------------	---

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	6
----------------	---

Quantity of section in width	1
------------------------------	---

Number of keys	1
----------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	2
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	No
-------------------------	----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	No
---------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP44
---------------------	------

Protection class	isol.class II
------------------	---------------