



FWB61S

**FWB encl.,univers,6-rows 72 modules cl.II IP44 w.plain door, 950x300x161mm,QC**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

Protection main switch No

**Configuration**

Number of modules 72

**Compatibility**

Suitable for Multimedia No

**Electric current**

Rated current 125 A

**Dimensions**

Insertion depth 161 mm

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 950 mm

Installation height 950 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 1 mm

**Cover, door**

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Copper weight of the product 0.042 kg

Colour white

RAL colour RAL 9010 - Pure white

**Installation, mounting**

Subject to technical modifications

Suitable for outdoor use

No

---

**Connection**

Number of conduit inlets

4

---

**Settings**

Enclosure type

Field distributor surface mounted

---

**Equipment**

Number of rows

6

Quantity of section in width

1

Number of keys

1

Can be accessorized

Yes

Number of openings for flange plates

2

Extension possible

Yes

Earthing terminal block

Yes

Neutral terminal block

Yes

Signal passing door

No

---

**Standards**

GWT Glow wire test

750 °C

European directive WEEE

concerned

Protection class according to IEC-61140

II

---

**Safety**

Protection index IP

IP44

Protection class

isol.class II