



FWB64GS

FWB encl. univers,surface mount.,IP44,classII,w. transp.door,950x1050x161mm,QC

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	288
-------------------	-----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	950 mm
Installation height	950 mm
Width of installed product	1050 mm
Width in division units	48
Thickness of sidewall material	1 mm

Cover, door

Number of keylock of the door	1
Cover type	With Notch
Door leave	double symmetric
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Equipment

Number of rows	24
Quantity of section in width	4
Number of keys	1
Quantity of rails	24
Can be accessorized	Yes
Number of openings for flange plates	8
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No