



FWB71

**FWB encl.,univers,7rows 84 mod cl.II IP44,plain door,1100x300x161mm,brass term.**

### Technical properties

#### Architecture

Fixing mode surface-mounting

#### Functions

With a pipe-in lead Yes

#### Configuration

Number of modules 84

#### Compatibility

Suitable for Multimedia No

#### Electric current

Rated current 125 A

#### Dimensions

Depth of installed product 165 mm

Internal depth 156 mm

Height of installed product 1100 mm

Installation height 1100 mm

Width of installed product 300 mm

Width in division units 12

Thickness of sidewall material 1 mm

#### Cover, door

Type of door closing hinged pattern handle

Number of keylock of the door 1

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

#### Materials

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

#### Installation, mounting

Suitable for outdoor use No

Subject to technical modifications

**Connection**

---

Number of conduit inlets	4
--------------------------	---

**Settings**

---

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

**Equipment**

---

Number of rows	7
----------------	---

---

Quantity of section in width	1
------------------------------	---

---

Number of keys	1
----------------	---

---

Quantity of rails	7
-------------------	---

---

Can be accessorized	Yes
---------------------	-----

---

Number of openings for flange plates	2
--------------------------------------	---

---

Extension possible	Yes
--------------------	-----

---

Earthing terminal block	No
-------------------------	----

---

Neutral terminal block	Yes
------------------------	-----

---

Signal passing door	No
---------------------	----

**Standards**

---

European directive WEEE	concerned
-------------------------	-----------

**Safety**

---

Protection index IP	IP44
---------------------	------

---

Protection class	isol.class II
------------------	---------------