



FWB73

FWB encl.,univers,7rows 252 mod cl.II IP44,plain door,1100x800x161mm,brass term.

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Module	with terminals
Number of modules	252

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	1100 mm
Installation height	1100 mm
Width of installed product	800 mm
Width in division units	36
Thickness of sidewall material	2 mm

Cover, door

Type of door closing	Hinged pattern handle and bar locking
Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Subject to technical modifications

Number of conduit inlets	12
--------------------------	----

Settings

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

Equipment

Number of rows	21
Quantity of section in width	3
Number of keys	1
Quantity of rails	21
Can be accessorized	Yes
Number of openings for flange plates	6
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	Yes
Signal passing door	No

Standards

Protection class according to IEC-61140	II
---	----

Safety

IK protection code against mechanical impacts	09
Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK09