



FWB73

FWB encl.,univers,7rows 252 mod cl.II IP44,plain door,1100x800x161mm,brass term.

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	252
-------------------	-----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth of installed product	165 mm
----------------------------	--------

Internal depth	156 mm
----------------	--------

Height of installed product	1100 mm
-----------------------------	---------

Installation height	1100 mm
---------------------	---------

Width of installed product	800 mm
----------------------------	--------

Width in division units	36
-------------------------	----

Thickness of sidewall material	2 mm
--------------------------------	------

Cover, door

Number of keylock of the door	1
-------------------------------	---

Cover type	With Notch
------------	------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	No
---------------------------	----

Materials

Colour	white
--------	-------

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Material	sheet steel
----------	-------------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	12
--------------------------	----

Equipment

Number of rows	21
Quantity of section in width	3
Number of keys	1
Quantity of rails	21
Can be accessorized	Yes
Number of openings for flange plates	6
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	Yes
Signal passing door	No

Standards

European directive WEEE	concerned
Protection class according to IEC-61140	II

Safety

Protection index IP	IP44
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No