



FWK3500600VERZ



fire-protection trunking smokeproof I90 FWK 30 50x60mm L=1, 5m galvanized

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	1500 mm
Internal width	59 mm
Trunking width	100 mm
Distance bottom-punch along trunking-direction	500 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	11
--	----

Cover, door

Lid shape	premounted
-----------	------------

Materials

Material group	steel, plaster
Type of surface treatment	Galvanised

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	2950 mm ²
-------------------------------	----------------------

Equipment

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	0

Standards

Testing institute	Dortmund
-------------------	----------

Safety

certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90