



FWK3500600VERZ



fire-protection trunking smokeproof I90 FWK 30 50x60mm L=1, 5m galvanized

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	1500 mm
Internal width	59 mm
Trunking width	100 mm
Distance bottom-punch along trunking-direction	500 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 11

Cover, door

Lid shape premounted

Materials

Material group steel, plaster

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 2950 mm²

Equipment

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	0

Standards

Testing institute Dortmund

Safety

REACH conform	Yes
RoHS conform	Yes
certificationnormfireprotductsystem	DIN 4102-11
classificationnormfireprotductsystem	DIN 4102-11
Fire resistance class	I 90