



FWK3501100VERZ



fire-protection trunking smokeproof I90 FWK 30 50x110mm L=1, 5m galvanized

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	1500 mm
Internal width	109 mm
Trunking width	150 mm
Distance bottom-punch along trunking-direction	500 mm
Distance bottom-punch crosswise trunking-direction	50 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 21

Cover, door

Lid shape premounted

Materials

Material group steel, plaster
 Type of surface treatment Galvanised

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 5450 mm²

Equipment

Number of fix dividers 0
 Number of pluggable separators 0
 Cable retainers per meter 0

Standards

Testing institute Dortmund

Safety

certificationnormfireproductsystem DIN 4102-11
 classificationnormfireproductsystem DIN 4102-11

