



FWK3502100VERZ



fire-protection trunking smokeproof I90 FWK 30 50x210mm L=1, 5m galvanized

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	50 mm
Trunking height	88 mm
Length	1500 mm
Internal width	209 mm
Trunking width	250 mm
Distance bottom-punch along trunking-direction	500 mm
Distance bottom-punch crosswise trunking-direction	150 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 43

Cover, door

Lid shape premounted

Materials

Material group steel, plaster

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 10450 mm²

Equipment

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	0

Standards

Testing institute Dortmund

Safety

REACH conform	Yes
RoHS conform	Yes
certificationnormfireproductsystem	DIN 4102-11

