



FWK3991600VERZ



fire-protection trunking smokeproof I90 FWK 30 100x160mm L=1m galvanized

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	102 mm
Trunking height	142 mm
Length	1000 mm
Internal width	159 mm
Trunking width	200 mm
Distance bottom-punch along trunking-direction	500 mm
Distance bottom-punch crosswise trunking-direction	100 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 65

Cover, door

Lid shape premounted

Materials

Material group steel, plaster
 Type of surface treatment Galvanised

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 16218 mm²

Equipment

Number of fix dividers 0
 Number of plugable separators 0
 Cable retainers per meter 0

Standards

Testing institute Dortmund

Safety

certificationnormfireproductsystem DIN 4102-11
 classificationnormfireproductsystem DIN 4102-11

