



FWK3992600VERZ



**fire-protection trunking smokeproof I90 FWK 30 100x260mm L=1m galvanized**

**Technical properties**

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Internal height	102 mm
Trunking height	142 mm
Length	1000 mm
Internal width	259 mm
Trunking width	300 mm
Distance bottom-punch along trunking-direction	500 mm
Distance bottom-punch crosswise trunking-direction	200 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 107

**Cover, door**

Lid shape premounted

**Materials**

Material group steel, plaster  
 Type of surface treatment Galvanised

**Installation, mounting**

Base punching With base punching

**Cable**

Internal/useful cross section 26418 mm<sup>2</sup>

**Equipment**

Number of fix dividers 0  
 Number of plugable separators 0  
 Cable retainers per meter 0

**Standards**

Testing institute Dortmund

**Safety**

certificationnormfireproductsystem DIN 4102-11  
 classificationnormfireproductsystem DIN 4102-11

