



FWK9500600VERZ



fire-protection trunking short circuit integrity E60/E30 FWK90 50x60 0, 75m ga

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	49 mm
Trunking height	142 mm
Length	750 mm
Internal width	54 mm
Trunking width	150 mm
Distance bottom-punch along trunking-direction	500 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 11

Cover, door

Lid shape premounted

Materials

Material group steel, plaster
Type of surface treatment Galvanised

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 2646 mm²

Equipment

Number of fix dividers 0
Number of plugable separators 0
Cable retainers per meter 0

Standards

Testing institute Dortmund - Stuttgart

Safety

certificationnormfireprotductsystem DIN 4102-12
classificationnormfireprotductsystem DIN 4102-12
Fire resistance class E 30 - E 60