



FWK9500600VERZ



**fire-protection trunking short circuit integrity E60/E30 FWK90 50x60 0, 75m ga**

**Technical properties**

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Internal height	49 mm
Trunking height	142 mm
Length	750 mm
Internal width	54 mm
Trunking width	150 mm
Distance bottom-punch along trunking-direction	500 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 11

**Cover, door**

Lid shape premounted

**Materials**

Material group steel, plaster

**Installation, mounting**

Base punching With base punching

**Cable**

Internal/useful cross section 2646 mm<sup>2</sup>

**Equipment**

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	0

**Standards**

Testing institute Dortmund - Stuttgart

**Safety**

REACH conform	Yes
RoHS conform	Yes
certificationnormfireprotductsystem	DIN 4102-12
classificationnormfireprotductsystem	DIN 4102-12
Fire resistance class	E 30 - E 60