



FWK9502100VERZ



fire-protection trunking short circuit integrity E60/E30 FWK90 50x210 0, 75m ga

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Internal height	49 mm
Trunking height	142 mm
Length	750 mm
Internal width	204 mm
Trunking width	300 mm
Distance bottom-punch along trunking-direction	500 mm
Distance bottom-punch crosswise trunking-direction	150 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 43

Cover, door

Lid shape premounted

Materials

Material group steel, plaster

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 9996 mm²

Equipment

Number of fix dividers	0
Number of plugable separators	0
Cable retainers per meter	0

Standards

Testing institute Dortmund - Stuttgart

Safety

REACH conform	No
RoHS conform	Yes
certificationnormfireproductsystem	DIN 4102-12

