



FWK9991600VERZ



fire-protection trunking short circuit integrity E90/E30 FWK90 100x160 0, 5m ga

Technical properties

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

| | |
|--|--------|
| Internal height | 103 mm |
| Trunking height | 196 mm |
| Length | 500 mm |
| Internal width | 154 mm |
| Trunking width | 250 mm |
| Distance bottom-punch along trunking-direction | 500 mm |
| Distance bottom-punch crosswise trunking-direction | 100 mm |

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 65

Cover, door

Lid shape premounted

Materials

Material group steel, plaster

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 15862 mm²

Equipment

| | |
|-------------------------------|---|
| Number of fix dividers | 0 |
| Number of plugable separators | 0 |
| Cable retainers per meter | 0 |

Standards

Testing institute Dortmund - Stuttgart

Safety

| | |
|------------------------------------|-------------|
| REACH conform | Yes |
| RoHS conform | Yes |
| certificationnormfireproductsystem | DIN 4102-12 |

