



Partition for wall trunkings without C-profile with punching pipe BRS/LFS

Technical properties

Architecture

Fixing mode Clamping

Configuration

Module 1 Gang

Antibacterial treatment No

Compatibility

Product compatibility BRSN / LFS

Dimensions

Trunking height 70 mm

Length 2000 mm

Materials

Material group plastic

Type of surface treatment untreated

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Impact strength IK07

Use conditions

Operating temperature -5...60 °C

G1612