



**Partition for wall trunkings without C-profile with punching pipe BRS/LFS**

**Technical properties**

**Architecture**

Fixing mode Clamping

**Configuration**

Antibacterial treatment No

**Compatibility**

Product compatibility BRSN / LFS

**Dimensions**

Trunking height 70 mm

Length 2000 mm

**Materials**

Material group plastic

Type of surface treatment untreated

**Standards**

European directive RoHS voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

Operating temperature -5...60 °C

G1612