




G32249010



Frontplate modular 2 x RJ45, 80mm, pure white

Technical properties

Architecture

| | |
|-------------|---------|
| Fixing mode | Screwed |
|-------------|---------|

Configuration

| | |
|---|---------------------------|
| kind of product (pre-cut lid for dado trunking) | Geräte mit Zentralscheibe |
|---|---------------------------|

Dimensions

| | |
|---------------------|--------|
| Length | 100 mm |
| width of opening | 52 mm |
| Height of opening | 52 mm |
| Diameter of opening | 0 mm |

Cover, door

| | |
|------------------------------|----------|
| Lid mounting | Internal |
| Lid width | 80 mm |
| Shape of cover for wall duct | Plain |

Materials

| | |
|---------------------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
| Material | PVC |
| Material group | plastic |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|----------|---------|
| Assembly | modular |
|----------|---------|

Equipment

| | |
|---|---|
| Number of outlets (pre-cut lid for dado trunking) | 1 |
|---|---|

temperatur

| | |
|---------------------|------------|
| Ambient temperature | -5...65 °C |
|---------------------|------------|