


G3234LAN



Frontplate modular 2 x RJ45, 80mm, halogen-free, painted alu

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Configuration

kind of product (pre-cut lid for dado trunking)	Geräte mit Zentralscheibe
---	---------------------------

Dimensions

Length	100 mm
width of opening	52 mm
Height of opening	52 mm
Diameter of opening	0 mm

Cover, door

Lid mounting	Internal
Lid width	80 mm
Shape of cover for wall duct	Plain

Materials

Colour	aluminium
Material	PC-ABS
Material group	plastic
Type of surface treatment	Painted

Installation, mounting

Assembly	modular
----------	---------

Equipment

Number of outlets (pre-cut lid for dado trunking)	1
---	---

temperatur

Ambient temperature	-30...90 °C
---------------------	-------------