


G3234LAN



**Frontplate modular 2 x RJ45, 80mm, halogen-free, painted alu**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Configuration**

kind of product (pre-cut lid for dado trunking) Geräte mit Zentralscheibe

Module 1 Gang

**Dimensions**

Length 100 mm

width of opening 52 mm

Height of opening 52 mm

Diameter of opening 0 mm

**Cover, door**

Lid mounting Internal

Lid width 80 mm

Shape of cover for wall duct Plain

**Materials**

Colour aluminium

Material PC-ABS

Material group plastic

Type of surface treatment Painted

**Installation, mounting**

Assembly modular

**Equipment**

Number of outlets (pre-cut lid for dado trunking) 1

**temperatur**

Ambient temperature -30...90 °C