



G3501LAN



Frontplate, halogen-free,nat.anod.

Technical properties

Architecture

Fixing mode Clamping

Configuration

kind of product (pre-cut lid for dado trunking) Kanalsteckdose 2-fach

Dimensions

Length 150 mm

width of opening 0 mm

Height of opening 0 mm

Diameter of opening 45 mm

Cover, door

Lid mounting Internal

Lid width 80 mm

Shape of cover for wall duct Plain

Materials

Colour aluminium

Material PC-ABS

Material group plastic

Installation, mounting

Assembly modular

Equipment

Number of outlets (pre-cut lid for dado trunking) 1

temperatur

Ambient temperature -30...90 °C