



G3501LAN



Frontplate, halogen-free,nat.anod.

Technical properties

Architecture

Fixing mode Clamping

Configuration

kind of product (pre-cut lid for dado trunking) Kanalsteckdose 2-fach

Module 2 Gang

Dimensions

Length 150 mm

width of opening 0 mm

Height of opening 0 mm

Diameter of opening 45 mm

Cover, door

Lid mounting Internal

Lid width 80 mm

Shape of cover for wall duct Plain

Materials

Material group plastic

Type of surface treatment Other

Installation, mounting

Assembly modular

Equipment

Number of outlets (pre-cut lid for dado trunking) 1

temperatur

Ambient temperature -30...90 °C