



G3561LAN



**Frontplate modular halogen-free,**

**Technical properties**

**Architecture**

Fixing mode Clipped

**Configuration**

kind of product (pre-cut lid for dado trunking) others

**Dimensions**

Length 10 mm

width of opening 0 mm

Height of opening 0 mm

Diameter of opening 0 mm

**Cover, door**

Lid mounting Internal

Lid width 80 mm

Shape of cover for wall duct Plain

**Materials**

Colour aluminium

Material PC-ABS

Material group plastic

Type of surface treatment Painted

**Equipment**

Number of outlets (pre-cut lid for dado trunking) 0

**Standards**

European directive RoHS voluntary compliance

**temperatur**

Ambient temperature -30...90 °C