



G3561LAN



Frontplate modular halogen-free,

Technical properties

Architecture

Fixing mode Clipped

Configuration

kind of product (pre-cut lid for dado trunking) others

Dimensions

Length 10 mm

width of opening 0 mm

Height of opening 0 mm

Diameter of opening 0 mm

Cover, door

Lid mounting Internal

Lid width 80 mm

Shape of cover for wall duct Plain

Materials

Material group plastic

Equipment

Number of outlets (pre-cut lid for dado trunking) 0

Standards

European directive RoHs voluntary compliance

temperatur

Ambient temperature -30...90 °C