



G4753

Supply cable, 3 poles, 750 mm

Technical properties

Architecture

Connection system Wago Winsta

Connectivity

Number of wires 3

Main electrical features

Nominal voltage 230 V

Electric current

Rated current 20 A

Dimensions

Length 750 mm

Length

Total length 0.75 m

Power

Fire load 2638 kJ

Resistance

Continuity resistor 1330 $\mu\Omega$

Materials

Colour black

Colour coding / contact insert black

Colour housing black

Colour outer sheath Black

Material Mixed materials

Material group mixed material

Connection

Cross section connection cable 2.5 mm²

Cable

Wire cross-section 2.5 mm²

Cable permanent temperature-resistant to 70 °C

Cable diameter 13 mm

Conductor cross-section 2.5 mm²

Equipment

Type side 1	Bus
Mechanical coding	Yes
Standards	
European directive RoHS	voluntary compliance
temperatur	
Insulating piece permanent temperature-resistant	105 °C