



G4797

**Supply cable, 3p, 2500mm**

**Technical properties**

**Architecture**

Connection system Wago Winsta

**Connectivity**

Number of wires 3

**Electric current**

Rated current 20 A

**Dimensions**

Length 2500 mm

**Length**

Total length 2.5 m

**Power**

Fire load 7152 kJ

**Resistance**

Continuity resistor 1330  $\mu\Omega$

**Materials**

Colour black

Colour coding / contact insert black

Colour housing black

Colour outer sheath Black

Material Mixed materials

Material group mixed material

**Connection**

Cross section connection cable 2.5 mm<sup>2</sup>

**Cable**

Wire cross-section 2.5 mm<sup>2</sup>

Cable permanent temperature-resistant to 70 °C

Cable diameter 13 mm

**Equipment**

Type side 1 Bus

Mechanical coding Yes

**Standards**

**Safety**

---

Protection index IP

IP20

**temperatur**

---

Insulating piece permanent temperature-resistant

105 °C