



G4798

Supply cable, 3p, 4500mm

Technical properties

Architecture

Connection system	Wago Winsta
-------------------	-------------

Connectivity

Number of wires	3
-----------------	---

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	20 A
---------------	------

Dimensions

Length	4500 mm
--------	---------

Length

Total length	4.5 m
--------------	-------

Power

Fire load	12462 kJ
-----------	----------

Resistance

Continuity resistor	1330 $\mu\Omega$
---------------------	------------------

Materials

Colour	black
--------	-------

Colour coding / contact insert	black
--------------------------------	-------

Colour housing	black
----------------	-------

Colour outer sheath	Black
---------------------	-------

Material	Mixed materials
----------	-----------------

Material group	mixed material
----------------	----------------

Connection

Cross section connection cable	2.5 mm ²
--------------------------------	---------------------

Cable

Wire cross-section	2.5 mm ²
--------------------	---------------------

Cable permanent temperature-resistant to	70 °C
--	-------

Cable diameter	13 mm
----------------	-------

Conductor cross-section	2.5 mm ²
-------------------------	---------------------

Equipment

Type side 1	Bus
Mechanical coding	Yes
Standards	
European directive RoHS	voluntary compliance
temperatur	
Insulating piece permanent temperature-resistant	105 °C