


G8360



Consolidation Point Wago 6x3-gang

Technical properties

Architecture

Connection system	Wago Winsta
Fixing mode	Clamping

Functions

Reconnectable	No
System-oriented connector system	Yes

Configuration

Module	6 Gang
--------	--------

Connectivity

Input	3-gang
-------	--------

Main electrical features

Nominal voltage	230 V
Type of supply voltage	AC

Electric current

Number of entry circuits	6
Rated current	16 A

Dimensions

Height of installed product	45 mm
Length	162 mm
Width of installed product	125 mm
Format	overhanging wiring accessory

Materials

Colour connector system	Black
RAL colour	RAL 7035 - Light grey
Material group	mixed material
Type of surface treatment	Other

Connection

Cross section connection cable	2.5 mm ²
Connector type	Clamp block
Number of accessible phases	2
Suitable for through-wiring	Yes

Equipment

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Place of installation	inaccessible
-----------------------	--------------