


G8360



## Consolidation Point Wago 6x3-gang

### Technical properties

#### Architecture

Connection system Wago Winsta

#### Functions

Reconnectable No  
 System-oriented connector system Yes

#### Configuration

Module 6 Gang

#### Connectivity

Input 3-gang

#### Main electrical features

Nominal voltage 230 V  
 Type of supply voltage AC

#### Electric current

Number of entry circuits 6  
 Rated current 16 A

#### Dimensions

Height of installed product 45 mm  
 Length 162 mm  
 Width of installed product 125 mm  
 Format overhanging wiring accessory

#### Materials

Colour connector system Black  
 RAL colour RAL 7035 - Light grey  
 Material group mixed material  
 Type of surface treatment Other

#### Connection

Cross section connection cable 2.5 mm<sup>2</sup>  
 Connector type Clamp block  
 Number of accessible phases 2  
 Suitable for through-wiring Yes

#### Equipment

Number of connection cables max. 6

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

---

Place of installation	inaccessible
-----------------------	--------------