



GBA500851ALU



Instal trunking-Base Alu 50085,anodised

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	45x45 mm
---------------------------------------	----------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	56 mm
Length	2000 mm
Trunking width	85 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	14 / 20
--	---------

Cover, door

Lid mounting	Internal
Lid width	45 mm
Number of lids mountable	1

Materials

Colour	aluminium
Material	Aluminium
Material group	aluminium

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Internal/useful cross section	4000 mm ²
-------------------------------	----------------------

Equipment

Number of plugable separators	1
Compartment quantity	1 / 2

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

Use conditions

Operating temperature

-5...90 °C