



GBA500851ALU



## Instal trunking-Base Alu 50085,anodised

### Technical properties

#### Configuration

Antibacterial treatment No

#### Compatibility

Device installation compatible format 45x45 mm

#### Connectivity

Trunking coupling Couplers as separate reference

#### Dimensions

Trunking height 56 mm

Length 2000 mm

Trunking width 85 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 14 / 20

#### Cover, door

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 1

#### Materials

Material group aluminium

#### Installation, mounting

Base punching Without base punching

#### Cable

Internal/useful cross section 4000 mm<sup>2</sup>

#### Equipment

Number of plugable separators 1

Compartment quantity 1 / 2

#### Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

#### Safety

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-5...90 °C