



GBA500851ALU



Instal trunking-Base Alu 50085,anodised

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	45x45 mm
---------------------------------------	----------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Dimensions

Trunking height	56 mm
Length	2000 mm
Trunking width	85 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	14 / 20
--	---------

Cover, door

Lid mounting	Internal
Lid width	45 mm
Number of lids mountable	1

Materials

Material group	aluminium
----------------	-----------

Installation, mounting

Base punching	Without base punching
---------------	-----------------------

Cable

Internal/useful cross section	4000 mm ²
-------------------------------	----------------------

Equipment

Number of plugable separators	1
Compartment quantity	1 / 2

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
Impact strength	IK07
Use conditions	
Operating temperature	-5...90 °C