



GBA501311ALU



**Install. trunking-Base Alu 50131,anodised.**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format 45x45 mm

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Trunking height 56 mm

Length 2000 mm

Trunking width 134 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 15 / 37

**Cover, door**

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 2

**Materials**

Material group aluminium

**Installation, mounting**

Base punching Without base punching

**Cable**

Internal/useful cross section 6500 mm<sup>2</sup>

**Equipment**

Number of plugable separators 2

Compartment quantity 2 / 4

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free	Yes
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-5...90 °C