



GBA501311ALU



Install. trunking-Base Alu 50131,anodised.

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format 45x45 mm

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 56 mm

Length 2000 mm

Trunking width 134 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 15 / 37

Cover, door

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 2

Materials

Colour aluminium

Material Aluminium

Material group aluminium

Installation, mounting

Base punching Without base punching

Cable

Internal/useful cross section 6500 mm²

Equipment

Number of plugable separators 2

Compartment quantity 2 / 4

Standards

European directive RoHS voluntary compliance

Safety

Use conditions

Operating temperature

-5...90 °C