



GBA501611ALU



**Install. trunking-Base Alu 50161,anodised.**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format 45x45 mm

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Trunking height 56 mm

Length 2000 mm

Trunking width 162 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 30 / 57

**Cover, door**

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 3

**Materials**

Colour aluminium

Material Aluminium

Material group aluminium

**Installation, mounting**

Base punching Without base punching

**Cable**

Internal/useful cross section 8000 mm<sup>2</sup>

**Equipment**

Compartment quantity 3

**Standards**

European directive RoHs voluntary compliance

**Safety**

Impact strength IK07

**Use conditions**

---

Operating temperature

-5...90 °C