



GBD5005009010



**Install. trunking GBD 50050, pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format 45x45 mm

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 54 mm

Length 2000 mm

Trunking width 54 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 4 / 15

**Cover, door**

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 1

**Materials**

Colour pure white

RAL colour RAL 9010 - Pure white

Material PVC

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching Without base punching

**Cable**

Internal/useful cross section 2500 mm<sup>2</sup>

**Equipment**

Number of pluggable separators 1

Compartment quantity 1 / 2

Cable retainers per meter 0

**Standards**

**Safety**

---

|                     |      |
|---------------------|------|
| Protection index IP | IP40 |
| REACH conform       | Yes  |
| RoHS conform        | Yes  |
| Halogen free        | No   |
| Impact strength     | IK07 |

**Use conditions**

---

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|

**temperatur**

---

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...60 °C |
|---------------------|------------|