



GBD5008509010



Install. trunking GBD 50085, pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format 45x45 mm

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 56 mm

Length 2000 mm

Trunking width 85 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 14 / 20

Cover, door

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 1

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 4500 mm²

Equipment

Number of pluggable separators 1

Compartment quantity 1 / 2

Cable retainers per meter 0

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...60 °C
---------------------	------------