



GBD5010009010



**Trunking GBD 50x100 pure white**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format Direct 45mm

**Connectivity**

Trunking coupling Couplers as separate reference

**Dimensions**

Trunking height 54 mm

Length 2000 mm

Trunking width 105 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 16 / 29

**Cover, door**

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 1

**Materials**

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching With base punching

**Cable**

Internal/useful cross section 4694 mm<sup>2</sup>

**Equipment**

Compartment quantity 1 / 2

Cable retainers per meter 0

**Standards**

European directive RoHS voluntary compliance

**Safety**

Impact strength

IK07

**Use conditions**

---

Operating temperature

-5...60 °C

**temperatur**

---

Ambient temperature

-5...65 °C