



GBD5010009010



Trunking GBD 50x100 pure white

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format Direct 45mm

Connectivity

Trunking coupling Couplers as separate reference

Dimensions

Trunking height 54 mm

Length 2000 mm

Trunking width 105 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 16 / 29

Cover, door

Lid mounting Internal

Lid width 45 mm

Number of lids mountable 1

Materials

RAL colour RAL 9010 - Pure white

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 4694 mm²

Equipment

Compartment quantity 1 / 2

Cable retainers per meter 0

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------