



GD102E

Mini-enclosure, gamma, 2 module, protect. class IP30

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Protection main switch No

Configuration

Number of modules 2

Compatibility

Suitable for Multimedia No

Electric current

Rated current 32 A

Dimensions

Depth of installed product 82 mm

Internal depth 82 mm

Height of installed product 160 mm

Width of installed product 55 mm

Width in division units 2

Cover, door

Type of door closing non keylock

Number of keylock of the door 0

Cover type With Notch

Door locking without

Cover type with notch

Transparent cover or door No

Materials

Colour white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Installation, mounting

Suitable for outdoor use No

Settings

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	No
Neutral terminal block	No

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II