



GD102N

**Mini-enclosure, gamma, 2 module, protect. class IP30**

**Technical properties**

**Functions**

With a pipe-in lead	Yes
Protection main switch	No

**Configuration**

Number of modules	2
-------------------	---

**Compatibility**

Suitable for Multimedia	No
-------------------------	----

**Main electrical features**

Nominal voltage	230 V
-----------------	-------

**Electric current**

Rated current	32 A
---------------	------

**Dimensions**

Depth of installed product	82 mm
Internal depth	82 mm
Height of installed product	160 mm
Width of installed product	55 mm
Width in division units	2

**Cover, door**

Type of door closing	non keylock
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	with notch
Transparent cover or door	No

**Materials**

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Settings**

**Equipment**

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	No
Neutral terminal block	No

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Halogen free	No