



GD102N

Mini-enclosure, gamma, 2 module, protect. class IP30

Technical properties

Functions

With a pipe-in lead	Yes
Protection main switch	No

Configuration

Number of modules	2
-------------------	---

Compatibility

Suitable for Multimedia	No
-------------------------	----

Main electrical features

Nominal voltage	230 V
-----------------	-------

Electric current

Rated current	32 A
---------------	------

Dimensions

Depth of installed product	82 mm
Internal depth	82 mm
Height of installed product	160 mm
Width of installed product	55 mm
Width in division units	2

Cover, door

Type of door closing	non keylock
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Cover type	with notch
Transparent cover or door	No

Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	No
Neutral terminal block	No

Safety

IK protection code against mechanical impacts	05
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No