



GD102N

**Mini-enclosure, gamma, 2 module, protect. class IP30**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes  
 Protection main switch No

**Configuration**

Number of modules 2

**Compatibility**

Suitable for Multimedia No

**Electric current**

Rated current 32 A

**Dimensions**

Depth of installed product 82 mm  
 Internal depth 82 mm  
 Height of installed product 160 mm  
 Width of installed product 55 mm  
 Width in division units 2

**Cover, door**

Type of door closing non keylock  
 Number of keylock of the door 0  
 Cover type With Notch  
 Door locking without  
 Cover type with notch  
 Transparent cover or door No

**Materials**

Colour white  
 Colour white  
 RAL colour RAL 9010 - Pure white  
 Material plastic

**Installation, mounting**

Suitable for outdoor use No

**Settings**

**Equipment**

---

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	No
Earthing terminal block	No
Neutral terminal block	No

**Standards**

---

European directive WEEE	concerned
-------------------------	-----------

**Safety**

---

IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II