



GD104N

**Mini-enclosure, gamma, 4 module, protect. class IP30, 1xPE, 1xN**

## Technical properties

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Functions

With a pipe-in lead	Yes
Protection main switch	No

### Configuration

Number of modules	4
-------------------	---

### Compatibility

Suitable for Multimedia	No
-------------------------	----

### Electric current

Rated current	40 A
---------------	------

### Dimensions

Depth of installed product	82 mm
Height of installed product	180 mm
Width of installed product	110 mm
Width in division units	4

### Cover, door

Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Transparent cover or door	No

### Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

### Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1

Can be accessorized	No
Earthing terminal block	Yes
Neutral terminal block	Yes

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP30
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No